

■ 2064 x 1544

■ 38 fps

Apex Series 

**USB**<sup>TM</sup>  
VISION

## ❖ AP-3200T-USB-LSX

3.2 megapixel CMOS prism area scan



- **High resolution prism-based 3-CMOS camera**
- **Full spatial resolution and true RGB color values with no interpolation**
- **Pre-screened to meet strict quality standards for dust/FODs in imaging path**
- **Available with or without IR-cut filter for applications needing extended red/NIR response**
- **Individual analog gain and exposure control for R, G, and B channels**
- **Color and edge enhancement functions**
- **On-board RGB to HSI, XYZ, sRGB and Adobe RGB color space conversions**
- **Single and multi-ROI's**
- **RGB video output with 8, 10, or 12-bits per channel\***
- **Compact size and white housing designed for clinical/laboratory environments**
- **Excellent shock and vibration resistance**
- **USB3 Vision interface**
- **C-mount lens mount**

\* Some video processing functions not available with 12-bit output



# Specifications for AP-3200T-USB-LSX

## Apex Series


| Specifications            | AP-3200T-USB-LSX                                                                                                                                                                                                                |
|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sensor                    | 1/1.8" 3-CMOS global shutter (IMX265)                                                                                                                                                                                           |
| Active pixels             | 2064 (h) x 1544 (v) x 3 (R,G,B)                                                                                                                                                                                                 |
| Frame rate, full frame    | 38.3 frames/sec. @ 8-bit                                                                                                                                                                                                        |
| Active area               | 7.12 mm (h) x 5.33 mm (v) - 8.89 mm diagonal                                                                                                                                                                                    |
| Pixel size                | 3.45 µm x 3.45 µm                                                                                                                                                                                                               |
| System clock              | 74.25 MHz (for pulse generator)                                                                                                                                                                                                 |
| Read-out modes            | Full ROI (single) 2064 (h) x 1544 (v) up to 38.3 fps<br>H: 16 to 2064 pixels in 16 pixel steps<br>V: 2 to 1544 lines in 2 line steps<br>ROI (multi) Binning Up to 5 overlapping scanning areas can be defined.<br>1X2, 2X1, 2X2 |
| EMVA 1288 Parameters      | 12-bit output format                                                                                                                                                                                                            |
| Absolute sensitivity      | 3.77 p (λ = 525 nm)                                                                                                                                                                                                             |
| Maximum SNR               | 40.39 dB                                                                                                                                                                                                                        |
| Traditional SNR*          | >60 dB (0 dB gain, 10-bit)                                                                                                                                                                                                      |
| Video signal output       | 8/10/12-bits per channel†<br>(24/30/36-bit RGB)                                                                                                                                                                                 |
| Video modes               | Normal, Single ROI, Multi ROI, Sequencer                                                                                                                                                                                        |
| Gain                      | Manual control - master mode or individual R/G/B channels<br>Auto gain control - off, continuous, one-push                                                                                                                      |
| White balance             | Off, 4 presets (3200K, 5000K, 6500K, 7500K), or one-push/continuous AWB using gain or exposure time (3000K to 9000K)                                                                                                            |
| Gamma/LUT                 | 0.45 to 1.0 (9 steps) or 257-point programmable LUT                                                                                                                                                                             |
| Shading correction        | Flat shading, color shading                                                                                                                                                                                                     |
| Trigger input             | Opto In (2), Pulse Generators (4), Software, NAND Out (2), User Output (4)                                                                                                                                                      |
| Exposure modes            | Timed/EPS, Trigger Width, Auto                                                                                                                                                                                                  |
| Electronic shutter        | (can be set independently for R/G/B channels)<br>30.73 µs to 8 sec. in 1 µs steps (8-bit)<br>34.73 µs to 8 sec. in 1 µs steps (10-bit)                                                                                          |
| Auto Level Control (ALC)  | Shutter range from 100 µs to 13.427 ms, gain range from 0 dB to +12 dB.<br>Tracking speeds and max. values adjustable.                                                                                                          |
| Pre-processing functions  | Color enhancer, edge enhancer, color space conversion (RGB to HSI, XYZ, sRGB, Adobe RGB), blemish compensation (200 px/channel)                                                                                                 |
| Operating temp. (ambient) | -5°C to +45°C (20 to 80% non-condensing)                                                                                                                                                                                        |
| Storage temp. (ambient)   | -25°C to +60°C (20 to 80% non condensing)                                                                                                                                                                                       |
| Vibration                 | 3G (20 Hz to 200 Hz, XYZ directions)                                                                                                                                                                                            |
| Shock                     | 50G                                                                                                                                                                                                                             |
| Regulations               | CE (EN61000-6-2, EN61000-6-3)<br>FCC Part 15 Class B, RoHS/WEEE                                                                                                                                                                 |
| Power                     | 12-pin USB 3.0 +12V to +24V DC ± 10%. 5.3 W typical @ +12 V<br>Bus power: not supported                                                                                                                                         |
| Lens mount                | C-mount                                                                                                                                                                                                                         |
| Dimensions (H x W x L)    | 44 mm x 44 mm x 74 mm (excl. connectors)                                                                                                                                                                                        |
| Weight                    | 170 g                                                                                                                                                                                                                           |

### Ordering Information

|                     |                                            |
|---------------------|--------------------------------------------|
| AP-3200T-USB-LSX    | 3-CMOS prism color camera with USB3 Vision |
| AP-3200T-USB-NF-LSX | Same as above with IR-cut filter removed   |


\*Traditional SNR is based on random noise in a single frame, where EMVA SNR measurements consider more comprehensive noise sources and variance over time.

### Dimensions



### Connector pin-out


#### DC In / Trigger



HIROSE HR10A-10R-12PB(71)

| Pin |                     |
|-----|---------------------|
| 1   | Ground              |
| 2   | DC in +12V to +24V  |
| 3   | Opto In 2-          |
| 4   | Opto In 2+          |
| 5   | Opto In 1-          |
| 6   | Opto In 1+          |
| 7   | Opto Out 1-         |
| 8   | Opto Out 1+         |
| 9   | TTL out 1           |
| 10  |                     |
| 11  | DC in +12V to +24 V |
| 12  | Ground              |


#### USB 3.0 Interface



Micro B type - ZX3600-B-10P or equiv.

| No. | I/O | Name      | Note                                |
|-----|-----|-----------|-------------------------------------|
| 1   | I   | VBUS IN   | Power (VBUS)                        |
| 2   | I/O | DM        | USB2.0 Differential pair (-)        |
| 3   | I/O | DP        | USB2.0 Differential pair (+)        |
| 4   |     | OTG ID    | USB OTG ID for identifying lines    |
| 5   |     | GND       | GND                                 |
| 6   | O   | FX3 SSTXM | USB3.0 Signal Transmission line (-) |
| 7   | O   | FX3 SSTXP | USB3.0 Signal Transmission line (+) |
| 8   |     | GND       | GND                                 |
| 9   | I   | FX3 SSRXP | USB3.0 Signal Receiving line (-)    |
| 10  | I   | FX3 SSRXM | USB3.0 Signal Receiving line (+)    |

### Spectral response



†12-bit output available in video processing bypass mode. See manual for details.

Europe, Middle East & Africa  
Phone +45 4457 8888  
Fax +45 4491 8880

Asia Pacific  
Phone +81 45 440 0154  
Fax +81 45 440 0166

Americas  
Phone (Toll-Free) 1 800 445 5444  
Phone +1 408 383 0300



Visit our website on [www.iai.com](http://www.iai.com)

See the possibilities