

❖ AD-o8o CL

2 CCD Multi-spectral camera




- Multi-spectral 2-channel CCD camera
- Advanced series 2 x 1/3" progressive scan camera
- Simultaneously captures Visible and Near-IR through the same optical path
- 1024 (h) x 768 (v) active pixels per channel
- 4.65 μm square pixels
- 30 frames/second with full resolution
- Increased frame rate with partial scan
- Programmable exposure from 20 μs to 33ms
- Pre-select and Pulse width trigger modes
- LVAL Synchronous/-asynchronous operation (auto-detect)
- Auto-iris lens video output allows a wider range of light
- RGB 24-bit or Raw Bayer 10 or 8-bit output for visible
- 10 or 8-bit output for Near-IR
- Setup by Windows NT/2000/XP via serial communication



Specifications for AD-o8o CL


Specifications		AD-o8o CL
Sensor	Visible Near-IR	1/3" color Bayer mosaic IT CCD 1/3" Monochrome interline transfer CCD
Pixel Clock		33.75 MHz
Frame rate full frame		30 frames/sec.
Active area		4.76 (h) x 3.57 (v) mm
Cell size		4.65 (h) x 4.65 (v) μ m
Active pixels		1024 (h) x 768 (v)
Color visible		Raw Bayer output, or RGB 24-bit
Read-out modes		
	Full	1024 (h) x 768 (v) 30 fps
	1/2 partial scan	1024 (h) x 384 (v) 48 fps
	1/4 partial scan	1024 (h) x 192 (v) 68 fps
	1/8 partial scan	1024 (h) x 96 (v) 86 fps
Sensitivity	Visible	1.4 Lux (On sensor, max. gain, shutter off, 50% video)
Sensitivity	Near-IR	0.1 μ W/cm ² at 800nm (On sensor, max. gain, shutter off, 50% video)
S/N ratio		>54dB (Gain 0 dB, shutter off)
Video output	Visible Near-IR	24-bits RGB or raw Bayer output 8 or 10 bit
Auto-iris lens video		0.7 Vp-p
Gain		-3dB to +12dB
Synchronization		Int. X-tal or ext. trigger
Inputs	Camera Link TTL	Ext. trigger, LVDS, (CC 1) Ext. Trigger 4V $\pm$ 2V
Outputs	Camera Link TTL	Clk., FVAL, LVAL, Data, EEN XEEN
Trigger modes		Pre Select, Pulse Width
Electronic shutter		
	Pre-set shutter	1/30 to 1/50,000 sec. in 12 steps
	Programmable exposure	0.5L to 792L (1LVAL unit)
	Pulse Width Control	1.5L to 60 frames
White balance		Only for RGB 24-bits output Gain range: -3dB to +6dB Manual: 3000K to 6500K One-push: 3000K to 6500K
Knee function		For 24-bit output (visible) Near-IR 8 or 10 bit Knee point, Knee slope
Control interface		Camera Link
Functions controlled by serial communication		Gain, shutter, trigger modes, read-out modes, bit depth
Indicators on rear panel		LED for power and trigger input
Operating Temperature		-5°C to +45°C
Humidity (operation)		20 - 80% non-condensing
Storage temp./humidity		-25°C to +60°C / 20 to 80%
Vibration		3 G (15Hz to 200 Hz XYZ)
Shock		50G
Regulations		CE (EN 61000-6-2, EN-61000-6-3), FCC part 15 class B, RoHS/WEEE
Power		12V DC $\pm$ 10% 4 W
Lens mount		C-mount
Dimensions (H x W x L)		55(H) x 55(W) x 80(D) mm
Weight		400 g

2CCD Prism



Connector pin-out

DC In / Trigger




HIROSE HR10A-10R-12PB-01

Pin	Signal
1	Ground
2	+12V DC
3	Ground
4	Auto Iris lens video output
5	Ground
6	XEEN 1 out
7	XEEN 2 out
8	Ground
9	Not used
10	Trigger 1 in
11	Trigger 2 in
12	Ground

Camera Link Interface

26 pin MDR connector 3M 10226-1A10JL




Pin	Signal	Function
1	14	GND
2	15	+/-Tx0
3	16	+/-Tx1
4	17	+/-Tx2
5	18	+/-Txclk
6	19	+/-Tx3
7	20	SerTC+/SerTC-
8	21	SerTFG+/SerTFG-
9	22	CC1-/CC1+
10	23	CC2-/CC2+
11	24	CC3-/CC3+
12	25	CC4-/CC4+
13	26	GND


Camera Link medium configuration.
*) Camera Link

Dimensions


Front view




Side view




Bottom view




Rear view



Near-IR Response AD-o8o CL



Visible Response AD-o8o CL



Ordering Information

AD-o8oCL Digital 2CCD Progressive Scan Multi-Spectral Camera

Europe, Middle East & Africa
Phone +45 4457 8888
Fax +45 4491 8880

Asia Pacific
Phone +81 45 440 0154
Fax +81 45 440 0166

Americas
Phone (Toll-Free) 1 800 445 5444
Phone +1 408 383 0300



See the possibilities

Visit our web site on www.jai.com